

[See all 3 Products in Family](#)

12" Diameter, Parabolic Reflector



Stock #53-875 **20+ In Stock**

MRP ₹7,971

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹7,971 each
Qty 11-25	₹7,164 each
Qty 26-49	₹6,760 each
Need More?	Request Quote

Product Downloads

General

Parabolic Mirror **Type:**

Physical & Mechanical Properties

304.80 **Diameter (mm):**

1.02 **Thickness (mm):**

0.75	Center Hole Diameter (inches):
12.0	Diameter (inches):
72.39	Height (mm):
0.04	Thickness (inches):
0.267	Weight (kg):

Optical Properties

Uncoated	Coating Type:
Uncoated	Coating:
76.20	Effective Focal Length EFL (mm):
Aluminum	Substrate: <input type="checkbox"/>
3.00	Effective Focal Length EFL (inches):
152.40	Radius of Curvature (mm):

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000	Imported By:

Product Details

- Ideal for Light Collection Applications
 - Features Center Hole and Mounting Rim
 - 12", 18", 24" Diameters Offered
- Large Parabolic Reflectors are ideal for a wide variety of light collection applications. Applications for these reflectors include solar energy collectors (solar furnaces), directional microphones, and detector systems. Each precision polished reflector is made from 0.04" thick aluminum and features a center hole and mounting rim. Large Parabolic Reflectors are uncoated. These reflectors are offered in 12", 18", and 24" diameters.