

**TECHSPEC® 13.5mm - 17mm Length, S-Mount Fine Focus Tube**



Stock #63-954 **20+ In Stock**

- 1 + MRP ₹7,264

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing

Qty 1-4	₹7,264 each
Qty 5-9	₹6,468 each
Qty 10-25	₹5,983 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Fine Focus Tube **Type:**  
Extension Tube (Adjustable) **Function:**

**Physical & Mechanical Properties**

13.5 - 17.0 **Extension Length (mm):**

10.0 Clear Aperture CA (mm):

20.0 Outer Diameter (mm):

## Threading & Mounting

S-Mount Thread Type:

M10 x 0.5 Barrel Thread:

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 235:

China Country of Origin:

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

**Note:** Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

## Technical Information

