

TECHSPEC®

135mm EFL Uncoated, UV-to-NIR Corrected Triplet



Stock **#47-312**

10 TO 12 DAYS

-

1

+

₹206,103.00

ADD TO CART

Qty 1-5
₹206,103.00
Qty 6+
₹175,218.00
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
135.00

Focal Length Tolerance (%):
±1.5 @ 248nm

Back Focal Length BFL (mm):
129.31

Back Focal Length BFL from Housing (mm):
126.9

Clear Aperture CA (mm): 22.5
Substrate: ☐ CaF ₂ / Fused Silica / CaF ₂
Surface Quality: 60-40
f#: 6.00
Numerical Aperture NA: 0.08
Coating: Uncoated
Effective Focal Length EFL @ 248nm (mm): 135.00
Housing Diameter (mm): 30.00 ±0.05
Housing Length (mm): 20.50 ±0.05
Type: Achromatic Triplet Lens
Wavelength Range (nm): 193 - 1000

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View