

TECHSPEC®

1400nm CWL, 25mm Dia. Hard Coated OD 4.0 25nm Bandpass Filter



Stock #87-831 [CONTACT US](#) [Additional Bandwidths](#)

1 **MRP ₹35,615**

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹35,615 each
Qty 6-25	₹28,451 each
Qty 26-49	₹26,712 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
eDrawing:eprt	
EO Spec Sheet	Download All

General

Type: Bandpass Filter

Physical & Mechanical Properties

Diameter (mm):	25.00 +0.0/-0.1	Clear Aperture CA (mm):	21.0
Thickness with Mount (mm):	5.00	Construction:	Mounted in Black Anodized Ring
Physical Durability:	Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2	Substrate Thickness (mm):	3.5 ±0.5

Optical Properties

Angle of Incidence (°):	0	Bandwidth (nm):	20
Optical Density OD (Average):	≥4.0	Center Wavelength CWL (nm):	1,400.00 ±3
Center Wavelength CWL Tolerance (nm):	±3	Full Width-Half Max FWHM (nm):	25.00 ±3
Full Width-Half Max	±3	Substrate:	Optical Glass

FWHM Tolerance (nm):			
Minimum Transmission (%):	>90	Coating:	Hard Coated
Surface Quality:	80-50	Blocking Wavelength Range (nm):	200 - 1800

Threading & Mounting

Mount Thickness (mm):	5.0 ±0.1		
------------------------------	----------	--	--

Environmental & Durability Factors

Environmental Durability:	Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7		
----------------------------------	---	--	--

Regulatory Compliance

RoHS 2015:	Compliant	Certificate of Conformance:	View
Reach 247:	Compliant		
Country of Origin:	United States	Imported By:	Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ideal for Life Science Instrumentation
- High Transmission, Deep Blocking
- Used to Prevent Photobleaching in Microscopy Applications
- Hard Coated OD 4.0 **5nm**, **10nm** and **50nm** Bandpass Filters also Available

TECHSPEC® Hard Coated OD 4.0 25nm Bandpass Filters are designed to be a midrange alternative to broadband or narrowband filters. These filters are ideal for fluorescence microscopy or other life science applications that rely on fluorescence detection such as flow cytometry or qPCR. TECHSPEC® Hard Coated OD 4.0 25nm Bandpass Filters can also be used to eliminate unwanted background noise while enhancing the signal-to-noise ratio in imaging or machine vision applications. The filters are designed to have a 0° angle of incidence and are mounted in a black anodized ring. Hard Coated OD 4.0 **5nm**, **10nm**, and **50nm** bandpass filters are also available.

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm² @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

Technical Information

All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.

Related Products



Manual Cage Filter Wheel



C, S, and T-Mount Circular Optic Mounts



Cotton-Tipped Swab Applicators



Hard Coated OD 4.0 10nm Bandpass Filters

Frequently Purchased Together



#52-105 - 4" x 5" Booklet, Commercial Grade Lens Tissue
₹1,567

Qty



#54-341 - Nikon F-Mount Lens to C-Mount Camera Adapter
₹9,027

Qty



#55-006 - 30mm, Multiple Filter Holder
₹10,896

Qty
























































#65-133 - 405nm CWL, 25mm Dia., Hard Coated OD 4.0 10nm Bandpass Filter
₹28,047

Qty

Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
	25.0/25.4mm Optic Dia., SM1 Thin Mount, M4	Fixed		#13-787	₹2,119 Request Quote	2 In Stock <input type="text" value="1"/>
	25.0/25.4mm Optic Dia., SM1 Thin Mount, 8-32	Fixed		#13-788	₹2,119 Request Quote	CONTACT US <input type="text" value="1"/>
	25.0mm Optic Dia., Optic Mount	Fixed		#64-560	₹3,305 Request Quote	CONTACT US <input type="text" value="1"/>
	25.0/25.4mm Optic Dia., E-Series Kinematic Mount	Adjustable - Tip-Tilt		#15-866	₹4,388 Request Quote	10 In Stock <input type="text" value="1"/>
	2.0 - 35.0mm Optic Dia., Three-Screw Adjustable Ring Mount	Fixed		#03-668	₹6,357 Request Quote	20+ In Stock <input type="text" value="1"/>

	Title	Type	Compare	Stock Number	Price	Buy
MORE+ 	25.0/25.4mm Optic Dia., L-Slot Direct Mount	Fixed		#36-410	₹6,861 Request Quote	9 In Stock <input type="text" value="1"/> 
MORE+ 	25.0/25.4mm Optic Dia., Side Flange Direct Mount	Fixed		#36-414	₹7,164 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	9.5 - 73.0mm Optic Dia., Three-Screw Adjustable Ring Mount	Fixed		#36-605	₹8,374 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	25.0/25.4mm Optic Dia., Kinematic Mount, 2-Screws	Adjustable - Tip-Tilt		#58-851	₹9,938 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	25.0/25.4mm Optic Dia., Optical Cell Assembly	Fixed		#36-461 CLEARANCE	₹10,190 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	25.0/25.4mm Optic Dia., L-Slot and Rotation Direct Mount	Adjustable - Rotary		#36-411	₹10,291 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	5.0 - 25.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-529	₹10,291 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	7.0 - 40.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-676	₹10,694 Request Quote	2 In Stock <input type="text" value="1"/> 
MORE+ 	25.0/25.4mm Optic Dia., Kinematic Mount, 3-Screws	Adjustable - Tip-Tilt		#58-854	₹10,796 Request Quote	20+ In Stock <input type="text" value="1"/> 
MORE+ 	10.0 - 60.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-530	₹10,896 Request Quote	CONTACT US <input type="text" value="1"/> 
MORE+ 	19.5 - 108.0mm Optic Dia., Three-Screw Adjustable Ring Mount	Fixed		#03-670	₹11,501 Request Quote	1 In Stock <input type="text" value="1"/> 
MORE+ 	7.0 - 67.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-669	₹11,703 Request Quote	6 In Stock <input type="text" value="1"/> 
MORE+ 	8.0 - 118.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-666	₹12,107 Request Quote	10 In Stock <input type="text" value="1"/> 
MORE+ 	4.0 - 36.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-077	₹15,840 Request Quote	6 In Stock <input type="text" value="1"/> 
MORE+ 	25.0/25.4mm Optic Dia., Stainless Steel Kinematic Mount, 2-Screws	Adjustable - Tip-Tilt		#26-815	₹16,244 Request Quote	4 In Stock <input type="text" value="1"/> 
MORE+ 	25.0/25.4mm Optic Dia., Stainless Steel Kinematic Mount, 3-Screws	Adjustable - Tip-Tilt		#26-818	₹18,362 Request Quote	9 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	25.0/25.4mm Optic Dia., X-Y Translating Optic Mount	Adjustable - Linear (XY)		#62-956	₹27,846 Request Quote	CONTACT US <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., Kinematic Mirror Mount	Adjustable - Tip-Tilt		#55-003	₹33,899 Request Quote	14 In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., Kinematic Mirror Mount with Micrometer	Adjustable - Tip-Tilt		#55-456	₹36,422 Request Quote	3 In Stock <input type="text" value="1"/> 
 	5.0 - 100.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-078	₹41,365 Request Quote	CONTACT US <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., Precision Gimbal Mount	Adjustable - Gimbal		#54-999	₹46,511 Request Quote	4 In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., X-Y-Z Translating Optic Mount	Adjustable - Linear (XYZ)		#62-959	₹54,481 Request Quote	6 In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., 5 Axes Optical Mount	Adjustable - Linear (XYZ) & Tip-Tilt		#13-776	₹76,173 Request Quote	2 In Stock <input type="text" value="1"/> 

Check out our full selection of mounts [here](#).