

104mm Max. Aperture, Iris Diaphragm



Stock #32-610 10 TO 12 DAYS

-

1

+

₹37,062.00

ADD TO CART

Qty 1-4
₹37,062.00
Qty 5+
₹32,695.00
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
5.0

Maximum Aperture (mm):
104.0

Outer Diameter (mm):
140.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 19.80
Number of Leaves: 16.00
Thickness (mm): 11.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)
