

14.0" Diameter, 24" Focal Length, Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock **#43-020** 10 TO 12 DAYS

- 1 + **₹22,185.00**

ADD TO CART

Qty 1-10
₹22,185.00
Qty 11+
₹19,184.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
355.60

Effective Focal Length EFL (mm):
609.60

Substrate: ☐
Acrylic

Coating:

Uncoated
Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.11
Diameter (inches): 14.0
Dimensional Tolerance (inches): ±0.05
Effective Diameter (inches): 12.9
Effective Focal Length EFL (inches): 24.00
Groove Density (grooves/inch): 200.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View