



150 x 150mm, 2mm Spacing, Glass Distortion Target



Stock #58-507 10 TO 12 DAYS

1

₹175,305.00

ADD TO CART

Qty 1-4
₹175,305.00
Qty 5+
₹166,614.00
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Reflective First Surface Chromium
R_{abs} = 50% ±5% @ 550nm

Dot Diameter (mm):
1.000

Dot Spacing (mm):

2.000
Substrate: Soda Lime Float Glass
Optical Density OD (Average): >3.0
Overall Accuracy (mm): ±0.0022
Pattern Size (mm): 150 x 150
Dimensions (inches): 7 x 7
Surface Quality: 40-20
Thickness (mm): 1.50
Type: Chrome on Glass
Dot Diameter Tolerance (mm): ± 0.002
Dot Spacing Tolerance (mm): ± 0.002 Center to Center
NIST Certification: Serialized NIST Traceable Certificate Included
Flatness (inches): 0.001

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
