

TECHSPEC® 150 x 150mm Linear Plastic Polarizer (XP42-200)



Stock **#86-196** 10 TO 12 DAYS

- 1 +

₹12,180.00

ADD TO CART

Qty 1+
₹12,180.00

Volume Pricing
Request Quote

Get Product Downloads

Extinction Ratio:
9000:1

Substrate: ☐
[XP42-200 on PMMA](#)

Length (mm):
150.00

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
150.0 x 150.0 +0.0/-1.0

Thickness (mm): 2.22 ±0.25
Transmission (%): Single: 42 Parallel: 36 Crossed: <0.004
Type: Linear Polarizer
Construction: Polarizing Film on PMMA
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98
Width (mm): 150.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant