

TECHSPEC®

15.0mm Dia. x 100.0mm FL, VIS-EXT Coated Plano-Convex Lens



Stock #88-702

10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹3,828.00

ADD TO CART

Qty 1-9
₹3,828.00
Qty 10+
₹3,437.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):
100.00 @587.6nm

Back Focal Length BFL (mm): 98.02
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.45
Radius R₁ (mm): 51.68
Clear Aperture CA (mm): 14
f/#: 6.67
Numerical Aperture NA: 0.07
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant