

TECHSPEC[®] 15.0mm Dia. x 22.5mm FL Uncoated, Plano-Convex Lens



Stock #32-004 [CONTACT US](#)
[Other Coating Options](#)

-

1

+

₹2,610.00

ADD TO CART

Qty 1-9
₹2,610.00
Qty 10+
₹2,349.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):
22.50 @ 587.6nm

Back Focal Length BFL (mm): 20.50
Coating: Uncoated
Substrate: 
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.35 ±0.10
Edge Thickness ET (mm): 1.36
Radius R₁ (mm): 15.12
Clear Aperture CA (mm): 14
f#: 1.5
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 380 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View