

TECHSPEC®

150mm Dia. Linear Plastic Polarizer (XP42-200)



Stock #86-203 10 TO 12 DAYS

- 1 +

₹12,180.00

ADD TO CART

Qty 1+
₹12,180.00

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
150.00 +0.0/-0.5

Extinction Ratio:
9000:1

Substrate: XP42-200 on PMMA

Operating Temperature (°C):
-40 to +80

Thickness (mm):
2.22 ±0.25

Transmission (%) : Single: 42 Parallel: 36 Crossed: <0.004
Type : Linear Polarizer
Construction : Polarizing Film on PMMA
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.98

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant