

LightPath 355110 | 1550nm Alignment, 0.40 NA Fiber Collimator w/ FC/PC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #83-726 CLEARANCE CONTACT US

-

1

+

₹10,261.65

ADD TO CART

Qty 1+

₹10,261.65

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):
6.24 @ 1150nm

Numerical Aperture NA:
0.40

Substrate: ☐
[D-ZLaF52LA](#)

Coating:

BBAR (1050-1600nm)
Coating Specification: R _{abs} <1.0% @ 1050 - 1600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.00
f/#: 1.25
Bevel: Protective bevel as needed
Connector: FC/PC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 13.00
Lightpath Lens Code: 355110
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 1050 - 1600
Conjugate Distance: Infinite
Lens Included: #87-127
Alignment Wavelength (nm): 1550

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
