

TECHSPEC® 15mm Dia., 0.33 Numerical Aperture, Uncoated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#37-422** [CONTACT US](#)

[Other Coating Options](#)

- 1 + **₹22,185.00**

ADD TO CART

Qty 1-5
₹22,185.00
Qty 6+
₹17,748.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
15.00 +0.00/-0.025

Effective Focal Length EFL (mm):
22.50 @ 587.6nm

Numerical Aperture NA:
0.33

Back Focal Length BFL (mm): 16.71
Substrate: N-BK7
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 13.75
Edge Thickness ET (mm): 6.25
Center Thickness CT (mm): 8.79 ±0.10
f/#: 1.50
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Conjugate Distance: Infinite
Power (diopters): 44.44

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant