

TECHSPEC® 15mm Dia., 0.40 Numerical Aperture, Uncoated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock #37-421 **20+ In Stock**

[Other Coating Options](#)

1 MRP ₹32,185

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹32,185 each
Qty 6-10	₹28,956 each
Qty 11-25	₹26,433 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

15.00 +0.00/-0.025 **Diameter (mm):**

<3	Centering (arcmin):
13.50	Clear Aperture CA (mm):
6.10	Edge Thickness ET (mm):
8.00 ±0.10	Center Thickness CT (mm):
Protective as needed	Bevel:

Plano	Shape of Back Surface:
-------	-------------------------------

Optical Properties

18.75 @587.6nm	Effective Focal Length EFL (mm):
----------------	---

0.40	Numerical Aperture NA:
------	-------------------------------

14.32	Back Focal Length BFL (mm):
-------	------------------------------------

N-SF6	Substrate: <input type="checkbox"/>
-----------------------	--

587.6	Aspheric Design Wavelength (nm):
-------	---

0.4λ	Asphere Figure Error, RMS @ 632.8nm:
------	---

Uncoated	Coating:
----------	-----------------

40-20	Surface Quality:
-------	-------------------------

1.25	f#:
------	------------

25.36	Abbe Number (v_d):
-------	-------------------------------------

1.805	Index of Refraction (n_d):
-------	---

390 - 2500	Wavelength Range (nm):
------------	-------------------------------

Infinite	Conjugate Distance:
----------	----------------------------

587.6	Focal Length Specification Wavelength (nm):
-------	--

53.33	Power (diopters):
-------	--------------------------

Material Properties

9.0	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
-----	---

Regulatory Compliance

Compliant	RoHS 2015:
---------------------------	-------------------

View	Certificate of Conformance:
----------------------	------------------------------------

Compliant	Reach 233:
---------------------------	-------------------

Singapore	Country of Origin:
-----------	---------------------------

Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:
---	---------------------

Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

Compatible Mounts
