

TECHSPEC®

15mm Dia., 0.66 Numerical Aperture, Uncoated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#37-419** 10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹23,925.00

ADD TO CART

Qty 1-5
₹23,925.00
Qty 6+
₹19,140.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
15.00 +0.00/-0.025

Effective Focal Length EFL (mm):
11.25 @ 587.6nm

Numerical Aperture NA:
0.66

Back Focal Length BFL (mm): 5.71
Substrate: N-SF6
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <1
Surface Quality: 40-20
Clear Aperture CA (mm): 13.50
Edge Thickness ET (mm): 6.67
Center Thickness CT (mm): 10.00 ±0.10
f/#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite
Power (diopters): 88.89

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant