

TECHSPEC[®] 15mm Dia. x 60mm FL, YAG-BBAR Coated, Inked, Double-Convex Lens



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock #89-253-INK 17 TO 22 D=DAYS

- 1 +

₹4,785.00

ADD TO CART

Qty 1-9

₹4,785.00

Qty 10+

₹4,307.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
15.00 ±0.025

Back Focal Length BFL (mm):
59.00

Effective Focal Length EFL (mm): 60.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R_{abs} <0.25% @ 532nm R_{abs} <0.25% @ 1064nm R_{avg} <1.0% @ 500 - 1100nm
Substrate:  N-BK7
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.08
Radius R₁=R₂ (mm): 61.5
Clear Aperture CA (mm): 14.00
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View