

70mm., 15mm Travel, Compact Motorized Linear Stage, English



70mm., 15mm Travel, Compact Motorized Linear Stage (Front)



Stock **#23-924** 10 TO 12 DAYS



1



₹59,160.00

ADD TO CART

Qty 1+

₹59,160.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Lead Screw

Type: English
Stage Size (mm): 70 x 107
Travel (mm): 15
Accuracy (µm): 5
Backlash (µm): 50
Construction: Aluminum, 3D Printed Plastic
Control Interface: USB-C
Height (mm): 33
Load Capacity (kg): 1
Mounting Threads: (9) 1/4-20, (4) 6-32, (8) 2-56
Note: Two integrated, adjustable limit switches Controller Required: #23-931
Operating Temperature (°C): 10-40
Parallelism (µm): 22
Repeatability (µm): 3
Resolution (µm): 5
Speed (mm/s): 40
Type of Motor: Stepper Motor
Weight (kg): 0.615
Computer Interface: USB-C
Maximum Operating Current (mA): 600
Min. Incremental Movement (µm): 1.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
