

TECHSPEC[®] 15mm, Uncoated, Fused Silica, Right Angle Prism



TECHSPEC UV Fused Silica Right Angle Prisms

Stock #45-184 10 TO 12 DAYS

-

1

+

₹7,830.00

ADD TO CART

Qty 1-5

₹7,830.00

Qty 6+

₹6,264.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:
Uncoated

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality:
60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.10 Legs
Angle Tolerance (arcmin): ±5
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 21.20
Length of Legs (mm): 15.00
Pyramid Tolerance (arcmin): ±5
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/2

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View