

[See all 20 Products in Family](#)

TECHSPEC® 15mm, VIS 0° Coated, Penta Prism



Stock **#48-597** [CONTACT US](#)

- 1 + MRP ₹10,998

i Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹10,998 each |
| Qty 6-25 | ₹8,778 each |
| Qty 26-49 | ₹8,273 each |
| Need More? | Request Quote |

Product Downloads

General

Penta Prism **Type:**

Physical & Mechanical Properties

15.00 **Length (mm):**

±0.10 **Dimensional Tolerance (mm):**

| | |
|--|--|
| Protective as needed | Bevel: |
| 15.00 | Length of Legs (mm): |
| Optical Properties | |
| VIS 0° & Aluminized | Coating: |
| N-BK7 | Substrate: <input type="checkbox"/> |
| 60-40 | Surface Quality: |
| Right-Handed | Image Orientation: |
| Coating Specification: Entrance/Exit Faces: $R_{avg} \leq 0.4\%$ @ 425 - 675nm Reflecting Surfaces: $R_{avg} > 85\%$ @ 400 - 700nm w/Black Overpaint | |
| 90 | Ray Deviation (°): |
| 425 - 675 | Wavelength Range (nm): |
| Damage Threshold, By Design: <input type="checkbox"/> Entrance & Exit Faces: 5 J/cm ² @ 532nm, 10ns Reflecting Surfaces: 0.3 J/cm ² @ 532 & 1064nm, 10ns | |
| ±5 | Beam Deviation Tolerance (arcmin): |
| 1.00 | Power (fringes) @ 632.8nm: |
| 0.25 | Irregularity (fringes) @ 632.8nm: |
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| Compliant | Reach 223: |
| View | Certificate of Conformance: |
| Singapore | Country of Origin: |
| Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Ray Deviation of 90°
- Right Handed Image
- Optical Tool for Defining a Right Angle
- Additional [Penta Prism](#) Options Available

TECHSPEC® N-BK7 Penta Prisms are five-sided prisms featuring a ray deviation of 90° and a right-handed image. The reflecting surfaces are aluminized. Slight movement of the prism does not affect the true right angle at which light rays are reflected, making a penta prism the ideal optical tool for defining a right angle in an optical system. TECHSPEC® N-BK7 Penta Prisms are made from precision N-BK7 for use in a variety of visible light applications. These prisms are offered with a VIS 0° or MgF2 coating, in a variety of sizes.

Technical Information



Penta Prism Ray Path



Penta Prism Tunnel Diagram

| Stock No. | Coating | Dimensions | |
|-----------|------------------|------------|-------|
| | | A | B |
| #85-159 | MS 0° | 0.50 | 0.60 |
| #85-160 | MS 0° | 1.00 | 1.20 |
| #45-112 | MgF ₂ | 5.00 | 6.10 |
| #48-595 | MS 0° | | |
| #32-030 | MgF ₂ | 10.00 | 11.95 |
| #48-596 | MS 0° | | |
| #43-502 | MgF ₂ | 15.00 | 15.96 |
| #48-597 | MS 0° | | |
| #31-051 | MgF ₂ | 20.00 | 21.65 |
| #48-598 | MS 0° | | |
| #42-779 | MgF ₂ | 25.00 | 27.90 |
| #47-458 | MgF ₂ | | |
| #48-599 | MS 0° | | |
| #45-073 | MgF ₂ | 30.00 | 32.47 |
| #48-600 | MS 0° | | |
| #45-402 | MgF ₂ | 35.00 | 37.88 |
| #48-601 | MS 0° | | |
| #45-674 | MgF ₂ | 40.00 | 43.30 |
| #48-602 | MS 0° | | |
| #45-675 | MgF ₂ | 45.00 | 48.71 |
| #48-603 | MS 0° | | |
| #45-676 | MgF ₂ | 50.00 | 54.12 |
| #47-459 | MgF ₂ | | |
| #48-604 | MS 0° | | |

