

TECHSPEC® 16 x 23mm Enhanced Aluminum, λ/4 Mirror



Stock **#43-506** 10 TO 12 DAYS

- 1 + **₹4,568.00**

ADD TO CART

Qty 1-5
₹4,568.00
Qty 6+
₹3,654.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: □
BOROFLOAT®

Back Surface:
Ground

Surface Quality:

60-40
Dimensions (mm): 16.0 x 23.0
Dimensional Tolerance (mm): +0/-0.5
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Length (mm): 23.00
Width (mm): 16.00
Damage Threshold, Reference: ☐ 0.2 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant