

**TECHSPEC® 1600nm 25mm Diameter , OD 2.0 Shortpass Filter**



TECHSPEC OD 2.0 Shortpass Filters

Stock **#84-656** 10 TO 12 DAYS

⊖ 1 ⊕ **₹11,832.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹11,832.00                    |
| Qty 6+                        |
| ₹10,057.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
25.00 +0.0/-0.2

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥2.0

|                                                                                                                                                   |
|---------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Cut-Off Wavelength (nm):</b><br>1,600.00                                                                                                       |
| <b>Substrate:</b> <br><a href="#">Fused Silica</a> (Coming 7980) |
| <b>Coating:</b><br>Traditional Coated                                                                                                             |
| <b>Rejection Wavelength (nm):</b><br>1700 - 2025                                                                                                  |
| <b>Surface Quality:</b><br>40-20                                                                                                                  |
| <b>Thickness (mm):</b><br>3.00                                                                                                                    |
| <b>Thickness Tolerance (mm):</b><br>±0.1                                                                                                          |
| <b>Transmission (%):</b><br>>85                                                                                                                   |
| <b>Transmission Wavelength (nm):</b><br>810 - 1540                                                                                                |
| <b>Type:</b><br>Shortpass Filter                                                                                                                  |
| <b>Clear Aperture (%):</b><br>80.00                                                                                                               |
| <b>Transmitted Wavefront, P-V:</b><br>λ/4                                                                                                         |
| <b>Slope Factor (%):</b><br>±3                                                                                                                    |
| <b>Cut-Off Tolerance (%):</b><br>±2                                                                                                               |
| <b>Wavelength Range (nm):</b><br>810 - 2025                                                                                                       |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |