

1.68mm FL, IR-Cut Filter at 650nm, f/2.5, Micro Video Lens



Stock #66-880 10 TO 12 DAYS

-

1

+

₹5,133.00

ADD TO CART

Qty 1-49
₹5,133.00
Qty 50+
₹4,089.00
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
13.20

Filter Thread:
M12 x 0.50

Maximum Diameter (mm):
15.0

Maximum Image Circle (mm):
4.50

Horizontal Field of View @ Max Sensor Format: 132.9
Resolution, On-Axis: 160 lp/mm @20% Contrast
Resolution, 0.7 Field: 80 lp/mm @20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 1.68
Maximum Sensor Format: 1/4"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mbunt)
Aperture (f/#): f/2.5
Distortion (%): -83.9 @Full Field
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View