

# 169 x 194mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#41-405** 10 TO 12 DAYS

- 1 + **₹6,134.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹6,134.00                     |
| Qty 6+                        |
| ₹4,916.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

Surface Flatness (P-V):  
4 - 6λ

Substrate: ☐  
Float Glass

Surface Quality:  
80-50

Dimensions (mm):

|                                                                     |
|---------------------------------------------------------------------|
| 169.0 x 194.0 ±0.76                                                 |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >85% @400 - 700nm |
| <b>Coating:</b><br>Protected Aluminum (400-700nm)                   |
| <b>Coating Type:</b><br>Metal                                       |
| <b>Angle of Incidence (°):</b><br>45.00                             |
| <b>Bevel:</b><br>Protective as needed                               |
| <b>Clear Aperture (%):</b><br>>90                                   |
| <b>Thickness (mm):</b><br>6.00                                      |
| <b>Type:</b><br>Flat Mirror                                         |
| <b>Wavelength Range (nm):</b><br>400 - 700                          |
| <b>Length (mm):</b><br>194.00                                       |
| <b>Width (mm):</b><br>169.00                                        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |