

[« See all 28 Products in Family](#)
[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#) / [HPr Series Fixed Focal Length Lenses](#)

# TECHSPEC® 16mm f/4, HPr Series Fixed Focal Length Lens



16mm HPr Series Fixed Focal Length Lens

Stock #36-513 **1 In Stock**

- 1 +

MRP ₹87,160

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹87,160 each
Need More?	<a href="#">Request Quote</a>

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	Zemax
eDrawing:eprt	
EO Spec Sheet	

## General

<b>Product Family:</b>	HPr Series	<b>Type:</b>	Fixed Focal Length Lens
------------------------	------------	--------------	-------------------------

## Physical & Mechanical Properties

<b>Iris Option:</b>	Fixed	<b>Length (mm):</b>	64.20
<b>Maximum Diameter (mm):</b>	48	<b>Outer Diameter (mm):</b>	48
<b>Weight (g):</b>	138	<b>Maximum Rear Protrusion (mm):</b>	0

## Optical Properties

<b>Horizontal Field of View @ Max Sensor Format:</b>	127mm - 53°	<b>Field of View at Max Sensor Format:</b>	Horizontal: 112.4mm - 47.2° Vertical: 82.7mm - 35.9° Diagonal: 144.7mm - 58°
<b>Horizontal Field of View, 1.1" Sensor:</b>	113.4mm - 47.6°	<b>Horizontal Field of View, 1" Sensor:</b>	101.3mm - 43.2°
<b>Horizontal Field of View, 2/3" Sensor:</b>	68.4mm - 30.1°	<b>Horizontal Field of View, 1/1.8" Sensor:</b>	55.7mm - 24.8°
<b>Horizontal Field of View, 1/2" Sensor:</b>	49.4mm - 22.1°	<b>Horizontal Field of View, 1/2.5" Sensor:</b>	44.7mm - 20.0°
<b>Horizontal Field of View, 1/3" Sensor:</b>	36.9mm - 16.6°	<b>Horizontal Field of View, 1/4" Sensor:</b>	27.6mm - 12.5°
<b>Maximum Image Circle (mm):</b>	17.60	<b>Numerical Aperture NA, Object Side:</b>	0.0159
<b>Number of Elements</b>	9 (7)	<b>Focal Length FL (mm):</b>	16.00

<b>Working Distance (mm):</b>	100 - ∞	<b>Aperture (f/#):</b>	f/4
<b>Coating:</b>	λ/4 MgF <sub>2</sub>	<b>Coating Specification:</b>	λ/4 MgF <sub>2</sub>
<b>Entrance Pupil Position (mm):</b>	27.28	<b>Object Space Principal Plane (mm):</b>	40.34
<b>Image Space Principal Plane (mm):</b>	4.08	<b>Maximum Distortion (%):</b>	-3.76
<b>Exit Pupil Position (mm):</b>	-58.81	<b>Optimized Working Distance (mm):</b>	400 - 2000
<b>Lens Wavelength Range:</b>	VIS		

## Sensor

<b>Maximum Sensor Format:</b>	1.1"	<b>Pixel Size (μm):</b>	1.85
-------------------------------	------	-------------------------	------

## Threading & Mounting

<b>Filter Thread:</b>	M46.0 x 0.75 (Female)	<b>Mount:</b>	C-Mount
-----------------------	-----------------------	---------------	---------

## Environmental & Durability Factors

<b>Storage Temperature (°C):</b>	<b>-20 to +60</b>	<b>Type of Ruggedization:</b>	Stabilized (Robust Mechanics for Shock and Vibration)
----------------------------------	-------------------	-------------------------------	---

## Regulatory Compliance

<b>Certificate of Conformance:</b>	<a href="#">View</a>		
<b>Country of Origin:</b>	China	<b>Imported By:</b>	Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000

## Product Details

- 1.1", C-Mount Lens
- Up to 20 MegaPixels, 1.85μm Pixel Size Sensors
- Ruggedized (HPr) Designs (50g Shock) of our HP Series Lens with Individual Optics Glued in Place
- 16mm to 50mm Focal Length
- **Instrumentation (HPi) Versions** Also Available

TECHSPEC® HPr Series Fixed Focal Length Lenses provide a stabilized ruggedization that maintains optical pointing stability after shock and vibration without sacrificing performance. This makes them ideal for calibrated imaging systems such as measurement and gauging, 3D stereo vision, robotics and sensing, autonomous vehicles, and object tracking. Every lens element is glued in place so that object to image mapping is always maintained. Additionally, the TECHSPEC HPr Series Fixed Focal Length Lenses feature a robust mechanical design with a simplified focus and stainless steel locking C-Mount clamp. Call for OEM Quantity Pricing.

Edmund Optics has created a family of high performance optical designs (the HP Series family) and developed three customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the HP Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **HP Series:** Features locking cam focus and iris adjustment. This is the most adjustable version of these optical designs and is the typical high quality machine vision lens.
- **HPi Series:** Simplified mechanics featuring fixed apertures with compact housing. **Industrial Ruggedization** for reduced size, cost, and locked focus.
- **HPr Series:** All optics glued in place and a locking C-clamp focus ring. **Stabilized Ruggedization** for reduced pixel shift and improved focus stability.

## Technical Information

#36-513, 16mm f/4, HPr Series Fixed Focal Length Lens, Distortion Plot

#36-513, 16mm f/4, HPr Series Fixed Focal Length Lens, Relative Illumination Plot

#36-513, 16mm f/4, HPr Series Fixed Focal Length Lens, Working Distance versus Field of View Plot

#36-513, 16mm f/4, HPr Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f4

#36-513, 16mm f/4, HPr Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f4

#36-513, 16mm f/4, HPr Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 2000mm Working Distance, f4

#36-513, 16mm f/4, HPr Series Fixed Focal Length Lens, Depth of Field Plot, 2000mm Working Distance, f4

## Accessories

**Note:** Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a>	Filter Adapter M34 x 0.5 from M27.5 x 0.5 (Female)		#11-610	₹5,788 <a href="#">Request Quote</a>	3 In Stock <input type="text" value="1"/>

## Related Products



#89-820 - Light Red M46.0 x 0.75 High Performance Machine Vision Filter  
₹30,469

Qty



#89-790 - Green M46.0 x 0.75 High Performance Machine Vision Filter  
₹30,469

Qty



#89-770 - Blue M46.0 x 0.75 High Performance Machine Vision Filter  
₹30,469

Qty



#89-800 - VIS (UV/IR Cut) M46.0 x 0.75 High Performance Machine Vision Filter  
₹30,469

Qty

## Frequently Purchased Together



#86-571 - 16mm Focal Length, HP Series Fixed Focal Length Lens



#36-511 - 16mm f/1.8, HPr Series Fixed Focal Length Lens



#54-857 - 18mm DG Series Fixed Focal Length Lens



#68-670 - 5mm FL Wide Angle Low Distortion Lens

₹72,216

Qty



₹87,160

Qty



₹60,762

Qty




































































₹93,228











































Qty



































































































## Compatible Cameras











































	Title	Type	Compare	Stock Number	Price	Buy
 	LUCID Vision Labs Phoenix™ PHX089S-CC, Sony IMX267, 8.9 MP, Color Camera	Color Camera		#11-469	₹97,173 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX089S-MC, Sony IMX267, 8.9 MP, Monochrome Camera	Monochrome Camera		#11-468	₹97,173 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI089S-CC, Sony IMX267, 8.9MP, Color Camera	Color Camera		#13-726	₹99,297 Request Quote	4 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI089S-MC, Sony IMX267, 8.9MP, Monochrome Camera	Monochrome Camera		#13-725	₹99,297 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2500-20gm Monochrome GigE Camera	Monochrome Camera		#35-919	₹1,11,510 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace acA2500-60um Monochrome USB 3.0 Camera	Monochrome Camera		#35-929	₹1,11,510 Request Quote	CONTACT US <input type="text" value="1"/> 
 	M2590, 1" Monochrome, DALSA Genie Nano GigE PoE Camera	Monochrome Camera		#34-964	₹1,12,572 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX120S-CC, Sony IMX304, 12.3 MP, Color Camera	Color Camera		#11-473	₹1,13,634 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Phoenix™ PHX120S-MC, Sony IMX304, 12.3 MP, Monochrome Camera	Monochrome Camera		#11-472	₹1,13,634 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Basler ace acA2500-20gc Color GigE Camera	Color Camera		#35-920	₹1,14,696 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace acA2500-60uc Color USB 3.0 Camera	Color Camera		#35-930	₹1,14,696 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI120S-CC, Sony IMX304, 12.3MP, Color Camera	Color Camera		#12-760	₹1,15,227 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Triton™ TRI120S-MC, Sony IMX304, 12.3MP, Monochrome Camera	Monochrome Camera		#12-759	₹1,15,227 Request Quote	1 In Stock <input type="text" value="1"/> 

































	Title	Type	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a> 	C2590-IR, 1" Color, DALSA Genie Nano GigE PoE Camera	Color Camera		#34-965	₹1,16,820 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	IDS U3-3180CP-C-HQ, USB 3.0, 1" Color Camera	Color Camera		#24-083	₹1,21,068 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	IDS U3-3180CP-M-GL, USB 3.0, 1" Monochrome Camera	Monochrome Camera		#24-084	₹1,21,068 <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	M2590, 1" NIR, Teledyne DALSA Genie Nano GigE PoE Camera	NIR Camera		#14-677	₹1,21,068 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	LUCID Vision Labs Triton™ TRI071S-CC, Sony IMX428, 7.1MP, Color Camera	Color Camera		#17-100	₹1,34,343 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	LUCID Vision Labs Triton™ TRI071S-MC, Sony IMX428, 7.1MP, Monochrome Camera	Monochrome Camera		#17-099	₹1,34,343 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	LUCID Vision Labs Triton™ TRI0162S-CC, Sony IMX542, 16.2MP, Color Camera	Color Camera		#17-103	₹1,40,715 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	LUCID Vision Labs Triton™ TRI0162S-MC, Sony IMX542, 16.2MP, Monochrome Camera	Monochrome Camera		#17-102	₹1,40,715 <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	GS3-U3-41C6C-C 1" FLIR Grasshopper®3 High Performance USB 3.0 Color Camera	Color Camera		#88-514	₹1,63,548 <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	GS3-U3-41C6M-C 1" FLIR Grasshopper®3 High Performance USB 3.0 Monochrome Camera	Monochrome Camera		#88-513	₹1,63,548 <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	GS3-U3-41C6NIR-C 1" FLIR Grasshopper®3 High Performance USB 3.0 NIR Camera	NIR Camera		#89-526	₹1,63,548 <a href="#">Request Quote</a>	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Allied Vision Alvium 1800 U-1620m, 1.1" 16.2MP C-Mount, Right Angle USB 3.1 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-602	₹1,65,672 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Allied Vision Alvium 1800 U-1620m, 1.1" 16.2MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-601	₹1,65,672 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 































	Title	Type	Compare	Stock Number	Price	Buy
 	Allied Vision Alvium 1800 U-1620c, 1.1" 16.2MP C-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)	Color Camera		#19-606	₹1,66,734 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-1620c, 1.1" 16.2MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#19-605	₹1,66,734 Request Quote	4 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-1620m, 1.1" 16.2MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#19-600	₹1,66,734 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-1620m, 1.1" 16.2MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#19-599	₹1,66,734 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-1620c, 1.1" 16.2MP C-Mount, Right Angle USB 3.1 Color Camera	Color Camera		#19-604	₹1,67,796 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-1620c, 1.1" 16.2MP C-Mount, USB 3.0 Color Camera	Color Camera		#19-603	₹1,67,796 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium G1-1620c, 1.1" 16.2MP C-Mount, GigE PoE Color Camera	Color Camera		#23-568	₹1,69,920 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium G1-1236m, 1.1" 12.4MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-563	₹1,69,920 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium G1-1236c, 1.1" 12.4MP C-Mount, GigE PoE Color Camera	Color Camera		#23-564	₹1,70,982 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-88S6C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#11-512	₹1,73,637 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-PGE-88S6C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#11-530	₹1,73,637 Request Quote	2 In Stock <input type="text" value="1"/> 
 	BFS-U3-88S6M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#11-511	₹1,73,637 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-PGE-88S6M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#11-529	₹1,73,637 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler AceacA4096-30um USB 3.0 Monochrome Camera	Monochrome Camera		#37-217	₹1,78,416 Request Quote	2 In Stock <input type="text" value="1"/> 

















































	Title	Type	Compare	Stock Number	Price	Buy
	 Basler ace acA4096-11gm Monochrome GigE Camera	Monochrome Camera		#37-209	₹1,78,416 Request Quote	CONTACT US <input type="text" value="1"/> 
	 LUCID Vision Labs Triton™ TRI0204S-CC, Sony IMX541, 20.4MP, Color Camera	Color Camera		#17-105	₹1,80,009 Request Quote	CONTACT US <input type="text" value="1"/> 
	 LUCID Vision Labs Triton™ TRI0204S-MC, Sony IMX541, 20.4MP, Monochrome Camera	Monochrome Camera		#17-104	₹1,80,009 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler Ace acA4096-30uc USB 3.0 Color Camera	Color Camera		#37-218	₹1,80,540 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace acA4096-11gc Color GigE Camera	Color Camera		#37-210	₹1,80,540 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Pixelink PL-D726MU-BL, 1" 6.6MP, Board Level USB 3.0 Monochrome Camera	Monochrome Camera		#89-402 <span style="background-color: red; color: white; padding: 2px;">CLEARANCE</span>	₹1,83,195 Request Quote	3 In Stock <input type="text" value="1"/> 
	 Basler ace2 a2A5320-23umBAS Monochrome USB3 Basic Camera	Monochrome Camera		#16-625	₹1,83,195 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A5320-7gmBAS Monochrome GigE Basic Camera	Monochrome Camera		#16-601	₹1,83,195 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A5320-23ucBAS Color USB3 Basic Camera	Color Camera		#16-626	₹1,85,319 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Basler ace2 a2A5320-7gcBAS Color GigE Basic Camera	Color Camera		#16-602	₹1,85,319 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Alvium 1800 U-1236m, 1.1" 12.4MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#14-891	₹1,85,728 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Mako G-419B 1" Monochrome CMOS Camera	Monochrome Camera		#88-472	₹1,87,146 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Mako G-419C 1" Color CMOS Camera	Color Camera		#88-473	₹1,89,036 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace acA2040-90um Monochrome USB 3.0 Camera	Monochrome Camera		#89-989	₹1,90,098 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Manta G-419 1" Monochrome CMOS Camera	Monochrome Camera		#88-458	₹1,90,926 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace acA2040-90uc Color USB 3.0 Camera	Color Camera		#89-990	₹1,94,346 Request Quote	1 In Stock <input type="text" value="1"/> 














































	Title	Type	Compare	Stock Number	Price	Buy
	 Allied Vision Manta G-419C Color CMOS PoE Camera	Color Camera		#13-941	₹1,96,597 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Manta G-419B Monochrome CMOS PoE Camera	Monochrome Camera		#13-940	₹1,96,597 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Mako G-419B 1" NIR CMOS Camera	NIR Camera		#88-474	₹1,97,543 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Alvium 1800 U-1236m, 1.1" 12.4MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#14-889	₹1,99,656 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium 1800 U-1236c, 1.1" 12.4MP C-Mount, USB 3.0 Color Camera	Color Camera		#14-890	₹2,00,718 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Allied Vision Alvium 1800 U-1236c, 1.1" 12.4MP C-Mount, Right Angle USB 3.1 Color Camera	Color Camera		#14-892	₹2,00,718 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A5320-23umPRO Monochrome USB3 Pro Camera	Monochrome Camera		#16-637	₹2,00,718 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A5320-7gmPRO Monochrome GigE Pro Camera	Monochrome Camera		#16-613	₹2,00,718 Request Quote	2 In Stock <input type="text" value="1"/> 
	 Pixelink M-Series M4C-CYL Microscopy Color Camera	Color Microscopy Camera		#17-819	₹2,01,249 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Manta G-419 1" NIR CMOS Camera	NIR Camera		#88-460	₹2,01,323 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A5320-23ucPRO Color USB3 Pro Camera	Color Camera		#16-638	₹2,04,435 Request Quote	CONTACT US <input type="text" value="1"/> 
	 Basler ace2 a2A5320-7gcPRO Color GigE Pro Camera	Color Camera		#16-614	₹2,04,435 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Alvium G1-1620m, 1.1" 16.2MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-567	₹2,05,954 Request Quote	CONTACT US <input type="text" value="1"/> 
	 IDS U3-3290SE-C-HQ, USB 3.0, 1" Color Camera	Color Camera		#24-134	₹2,06,559 Request Quote	CONTACT US <input type="text" value="1"/> 
	 IDS U3-3290SE-M-GL, USB 3.0, 1" Monochrome Camera	Monochrome Camera		#24-135	₹2,06,559 Request Quote	1 In Stock <input type="text" value="1"/> 
	 Allied Vision Manta G-1236C Color CMOS PoE Camera	Color Camera		#37-515 <b>CLEARANCE</b>	₹2,07,510 Request Quote	2 In Stock <input type="text" value="1"/> 

















































	Title	Type	Compare	Stock Number	Price	Buy
 	Allied Vision Manta G-895 1" Color CMOS Camera	Color Camera		#36-179	₹2,08,152 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Manta G-895 1" Monochrome CMOS Camera	Monochrome Camera		#36-178	₹2,08,152 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium G1-2040m, 1.1" 20.4MP C-Mount, GigE PoE Monochrome Camera	Monochrome Camera		#23-571	₹2,08,152 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-2040m, 1.1" 20.4MP C-Mount, Right Angle USB 3.1 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-610	₹2,11,338 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-2040m, 1.1" 20.4MP C-Mount, USB 3.0 Monochrome Camera (Partial Housing)	Monochrome Camera		#19-609	₹2,11,338 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-2040c, 1.1" 20.4MP C-Mount, Right Angle USB 3.1 Color Camera (Partial Housing)	Color Camera		#19-614	₹2,12,400 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-2040c, 1.1" 20.4MP C-Mount, USB 3.0 Color Camera (Partial Housing)	Color Camera		#19-613	₹2,12,400 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-2040m, 1.1" 20.4MP C-Mount, Right Angle USB 3.1 Monochrome Camera	Monochrome Camera		#19-608	₹2,12,400 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-2040m, 1.1" 20.4MP C-Mount, USB 3.0 Monochrome Camera	Monochrome Camera		#19-607	₹2,12,400 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-122S6C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#11-518	₹2,14,524 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-895C Color CMOS PoE Camera	Color Camera		#35-899	₹2,14,524 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-PGE-122S6C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#11-532	₹2,14,524 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-2040c, 1.1" 20.4MP C-Mount, USB 3.0 Color Camera	Color Camera		#19-611	₹2,14,524 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Alvium 1800 U-2040c, 1.1" 20.4MP C-Mount,	Color Camera		#19-612	₹2,14,524 Request Quote	2 In Stock <input type="text" value="1"/> 











































	Title	Type	Compare	Stock Number	Price	Buy
	Right Angle USB 3.1 Color Camera					
<a href="#">MORE+</a> 	BFS-U3-122S6M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#11-517	₹2,14,524 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Allied Vision Manta G-895B Monochrome CMOS PoE Camera	Monochrome Camera		#35-898	₹2,14,524 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	BFS-PGE-122S6M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#11-531	₹2,14,524 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Allied Vision Manta G-1620C Color CMOS PoE Camera	Color Camera		#17-092	₹2,15,586 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Allied Vision Manta G-1620B Monochrome CMOS PoE Camera	Monochrome Camera		#17-091	₹2,15,586 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Allied Vision Alvium G5-1620m, 1.1" 16.2MP C-Mount, 5GigE PoE Monochrome Camera	Monochrome Camera		#23-635	₹2,16,648 <a href="#">Request Quote</a>	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Allied Vision Alvium G5-1620c, 1.1" 16.2MP C-Mount, 5GigE PoE Color Camera	Color Camera		#23-636	₹2,17,710 <a href="#">Request Quote</a>	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler Ace acA4112-20um USB 3.0 Monochrome Camera	Monochrome Camera		#37-221	₹2,18,772 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler ace acA4112-8gm Monochrome GigE Camera	Monochrome Camera		#37-211	₹2,18,772 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler Ace acA4112-20uc USB 3.0 Color Camera	Color Camera		#37-222	₹2,20,896 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler ace acA4112-8gc Color GigE Camera	Color Camera		#37-212	₹2,20,896 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler ace acA2040-90um NIR USB 3.0 Camera	NIR Camera		#34-176	₹2,25,144 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	BFS-U3-70S7C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#13-927	₹2,28,330 <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	BFS-PGE-70S7C-C PoE GigE Blackfly® S, Color Camera	Color Camera		#13-923	₹2,28,330 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	BFS-U3-70S7M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#13-926	₹2,28,330 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	BFS-PGE-70S7M-C PoE GigE Blackfly® S, Monochrome Camera	Monochrome Camera		#13-922	₹2,28,330 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
























	Title	Type	Compare	Stock Number	Price	Buy
<a href="#">MORE+</a> 	Pixelink PL-D734CU-T, 1" 4.2MP, C-Mount USB 3.0 Color Camera	Color Camera		#33-343	₹2,29,392 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Pixelink PL-D797CU-BL, 1.1" 7.1MP, Board Level USB 3.0 Color Camera	Color Camera		#14-170	₹2,29,392 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Pixelink PL-D734MU-T, 1" 4.2MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#33-342	₹2,29,392 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Pixelink PL-D797MU-BL, 1.1" 7.1MP, Board Level USB 3.0 Monochrome Camera	Monochrome Camera		#14-169	₹2,29,392 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler ace2 a2A4504-18umBAS Monochrome USB3 Basic Camera	Monochrome Camera		#16-623	₹2,30,454 <a href="#">Request Quote</a>	2 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler ace2 a2A4504-5gmBAS Monochrome GigE Basic Camera	Monochrome Camera		#16-599	₹2,30,454 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler ace2 a2A4504-18ucBAS Color USB3 Basic Camera	Color Camera		#16-624	₹2,34,171 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler ace2 a2A4504-5gcBAS Color GigE Basic Camera	Color Camera		#16-600	₹2,34,171 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler ace acA2040-25gm Monochrome GigE Camera	Monochrome Camera		#87-104	₹2,36,826 <a href="#">Request Quote</a>	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Pixelink PL-D797CU-T, 1.1" 7.1MP, C-Mount USB 3.0 Color Camera	Color Camera		#14-168	₹2,40,543 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	LUCID Vision Labs Atlas™ ATL071S-CC, Sony IMX420, 7.1MP, Color Camera	Color Camera		#17-111	₹2,40,543 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Pixelink PL-D797MU-T, 1.1" 7.1MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#14-167	₹2,40,543 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	LUCID Vision Labs Atlas™ ATL071S-MC, Sony IMX420, 7.1MP, Monochrome Camera	Monochrome Camera		#17-110	₹2,40,543 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Basler ace acA2040-25gc Color GigE Camera	Color Camera		#87-105	₹2,41,074 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Pixelink M-Series M4M-CYL Microscopy Monochrome Camera	Monochrome Microscopy Camera		#17-820	₹2,52,225 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	Allied Vision Alvium G1-2040c, 1.1" 20.4MP C-Mount, GigE PoE Color Camera	Color Camera		#23-572	₹2,55,273 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace2 a2A4504-18umPRO Monochrome USB3 Pro Camera	Monochrome Camera		#16-635	₹2,55,411 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace2 a2A4504-5gmPRO Monochrome GigE Pro Camera	Monochrome Camera		#16-611	₹2,55,411 Request Quote	CONTACT US <input type="text" value="1"/> 
 	IDS U3-3200SE-C-HQ, USB 3.0, 1.1" Color Camera	Color Camera		#24-132	₹2,56,473 Request Quote	1 In Stock <input type="text" value="1"/> 
 	IDS U3-3200SE-M-GL, USB 3.0, 1.1" Monochrome Camera	Monochrome Camera		#24-133	₹2,56,473 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler ace2 a2A4504-18ucPRO Color USB3 Pro Camera	Color Camera		#16-636	₹2,58,066 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler ace2 a2A4504-5gcPRO Color GigE Pro Camera	Color Camera		#16-612	₹2,58,066 Request Quote	CONTACT US <input type="text" value="1"/> 
 	M4020, 1.1" Monochrome, DALSA Genie Nano GigE PoE Camera	Monochrome Camera		#35-911	₹2,58,597 Request Quote	CONTACT US <input type="text" value="1"/> 
 	C4020-IR, 1.1" Color, DALSA Genie Nano GigE PoE Camera	Color Camera		#35-912	₹2,60,721 Request Quote	3 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-2040B Monochrome CMOS PoE Camera	Monochrome Camera		#17-093	₹2,62,314 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink PL-D799CU-T, 1" 9.0MP, C-Mount USB 3.0 Color Camera	Color Camera		#38-008	₹2,63,376 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D799MU-T, 1" 9.0MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#38-007	₹2,63,376 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-1236 1.1" Color CMOS Camera	Color Camera		#36-181	₹2,65,500 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-1236 1.1" Monochrome CMOS Camera	Monochrome Camera		#36-180	₹2,65,500 Request Quote	CONTACT US <input type="text" value="1"/> 
 	IDS U3-3990SE-C-HQ, USB 3.0, 1.1" Color Camera	Color Camera		#24-140	₹2,66,031 Request Quote	3 In Stock <input type="text" value="1"/> 
 	IDS U3-3990SE-M-GL, USB 3.0, 1.1" Monochrome Camera	Monochrome Camera		#24-141	₹2,66,031 Request Quote	2 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	Basler ace acA2040-25gm-NIR GigE Camera	NIR Camera		#87-106	₹2,68,686 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Allied Vision Manta G-1236B Monochrome CMOS PoE Camera	Monochrome Camera		#37-514	₹2,71,872 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Atlas™ ATL089S-CC, Sony IMX255, 8.9MP, Color Camera	Color Camera		#13-736	₹2,72,934 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Atlas™ ATL089S-MC, Sony IMX255, 8.9MP, Monochrome Camera	Monochrome Camera		#13-735	₹2,72,934 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink PL-D757CU-BL, 1.1" 7.1MP, Board Level USB 3.0 Color Camera	Color Camera		#14-166	₹2,86,740 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink PL-D757MU-BL, 1.1" 7.1MP, Board Level USB 3.0 Monochrome Camera	Monochrome Camera		#14-165	₹2,86,740 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink M-Series M9C-CYL Microscopy Color Camera	Color Microscopy Camera		#17-825	₹2,87,271 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink M-Series M9M-CYL Microscopy Monochrome Camera	Monochrome Microscopy Camera		#17-826	₹2,87,271 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Prosilica GT2050 1" Color CMOS Camera	Color Camera		#87-082	₹2,98,422 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink PL-D757CU-T, 1.1" 7.1MP, C-Mount USB 3.0 Color Camera	Color Camera		#14-164	₹2,98,422 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Allied Vision Prosilica GT2050 1" Monochrome CMOS Camera	Monochrome Camera		#87-081	₹2,98,422 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D757MU-T, 1.1" 7.1MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#14-163	₹2,98,422 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Atlas™ ATL120S-CC, Sony IMX253, 12.3MP, Color Camera	Color Camera		#13-734	₹3,05,856 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Atlas™ ATL120S-MC, Sony IMX253, 12.3MP, Monochrome Camera	Monochrome Camera		#13-733	₹3,05,856 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink PL-D7912CU-T, 1.1" 12MP, C-Mount USB 3.0 Color Camera	Color Camera		#38-010	₹3,09,573 Request Quote	CONTACT US <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	Pixelink PL-D7912MU-T, 1.1" 12MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#38-009	₹3,09,573 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-89S6C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#11-514	₹3,11,166 Request Quote	CONTACT US <input type="text" value="1"/> 
 	BFS-U3-89S6M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#11-513	₹3,11,166 Request Quote	1 In Stock <input type="text" value="1"/> 
 	M4060, 1" Monochrome, Teledyne DALSA Genie Nano 5GigE PoE Camera	Monochrome Camera		#16-030	₹3,15,945 Request Quote	1 In Stock <input type="text" value="1"/> 
 	C4060-IR, 1" Color, Teledyne DALSA Genie Nano 5GigE PoE Camera	Color Camera		#16-031	₹3,17,538 Request Quote	13 In Stock <input type="text" value="1"/> 
 	Basler Ace acA4096-40uc USB 3.0 Color Camera	Color Camera		#37-220	₹3,32,406 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D759CU-BL, 1" 8.9MP, Board Level USB 3.0 Color Camera	Color Camera		#11-443	₹3,32,406 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink M-Series M12BC-CYL Microscopy Color Camera	Color Microscopy Camera		#17-809	₹3,32,406 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D759MU-BL, 1" 8.9MP, Board Level USB 3.0 Monochrome Camera	Monochrome Camera		#11-442	₹3,32,406 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink M-Series M12BM-CYL Microscopy Monochrome Camera	Monochrome Microscopy Camera		#17-810	₹3,32,406 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Oryx® ORX-10G-71S7C-C Color 10GigE	Color Camera		#20-251	₹3,33,468 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Oryx® ORX-10G-71S7M-C Mono 10GigE	Monochrome Camera		#20-250	₹3,33,468 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink PL-D759CU-T, 1" 8.9MP, C-Mount USB 3.0 Color Camera	Color Camera		#11-441	₹3,44,088 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D759MU-T, 1" 8.9MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#11-440	₹3,44,088 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-123S6C-C USB 3.1 Blackfly® S, Color Camera	Color Camera		#11-520	₹3,47,274 Request Quote	1 In Stock <input type="text" value="1"/> 
 	BFS-U3-123S6M-C USB 3.1 Blackfly® S, Monochrome Camera	Monochrome Camera		#11-519	₹3,47,274 Request Quote	1 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
 	M4040, 1.1" Monochrome, Teledyne DALSA Genie Nano GigE PoE Camera	Monochrome Camera		#14-697	₹3,52,053 Request Quote	CONTACT US <input type="text" value="1"/> 
 	C4040-IR, 1.1" Color, Teledyne DALSA Genie Nano GigE PoE Camera	Color Camera		#14-698	₹3,54,177 Request Quote	CONTACT US <input type="text" value="1"/> 
 	LUCID Vision Labs Atlas10 ATX162S-CC, Sony IMX532, 16.2MP, Color Camera	Color Camera		#17-119	₹3,55,770 Request Quote	1 In Stock <input type="text" value="1"/> 
 	LUCID Vision Labs Atlas10 ATX162S-MC, Sony IMX532, 16.2MP, Monochrome Camera	Monochrome Camera		#17-118	₹3,55,770 Request Quote	CONTACT US <input type="text" value="1"/> 
 	GS3-U3-89S6C-C 1" FLIR Grasshopper®3 High Performance USB 3.0 Color Camera	Color Camera		#36-338	₹3,60,549 Request Quote	1 In Stock <input type="text" value="1"/> 
 	GS3-U3-89S6M-C 1" FLIR Grasshopper®3 High Performance USB 3.0 Monochrome Camera	Monochrome Camera		#36-337	₹3,60,549 Request Quote	4 In Stock <input type="text" value="1"/> 
 	M4040, 1.1" Monochrome, Teledyne DALSA Genie Nano 5GigE PoE Camera	Monochrome Camera		#16-028	₹3,64,266 Request Quote	CONTACT US <input type="text" value="1"/> 
 	C4040-IR, 1.1" Color, Teledyne DALSA Genie Nano 5GigE PoE Camera	Color Camera		#16-029	₹3,66,390 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Basler Ace acA4112-30um USB 3.0 Monochrome Camera	Monochrome Camera		#37-223	₹3,72,762 Request Quote	1 In Stock <input type="text" value="1"/> 
 	Basler Ace acA4112-30uc USB 3.0 Color Camera	Color Camera		#37-224	₹3,77,010 Request Quote	2 In Stock <input type="text" value="1"/> 
 	Pixelink PL-D7512CU-BL, 1.1" 12.3MP, Board Level USB 3.0 Color Camera	Color Camera		#11-447	₹3,78,072 Request Quote	CONTACT US <input type="text" value="1"/> 
 	Pixelink PL-D7512MU-BL, 1.1" 12.3MP, Board Level USB 3.0 Monochrome Camera	Monochrome Camera		#11-446	₹3,78,072 Request Quote	CONTACT US <input type="text" value="1"/> 
 	GS3-U3-123S6C-C 1.1" FLIR Grasshopper®3 High Performance USB 3.0 Color Camera	Color Camera		#36-340	₹3,86,037 Request Quote	1 In Stock <input type="text" value="1"/> 
 	GS3-U3-123S6M-C 1.1" FLIR Grasshopper®3 High Performance USB 3.0 Monochrome Camera	Monochrome Camera		#36-339	₹3,86,037 Request Quote	2 In Stock <input type="text" value="1"/> 

	Title	Type	Compare	Stock Number	Price	Buy
	Monochrome Camera					
<a href="#">MORE+</a> 	Pixelink PL-D7512CU-T, 1.1" 12.3MP, C-Mount USB 3.0 Color Camera	Color Camera		#11-445	₹3,89,754 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Pixelink PL-D7512MU-T, 1.1" 12.3MP, C-Mount USB 3.0 Monochrome Camera	Monochrome Camera		#11-444	₹3,89,754 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Pixelink M-Series M12C-CYL Microscopy Color Camera	Color Microscopy Camera		#17-811	₹4,01,436 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Pixelink M-Series M12M-CYL Microscopy Monochrome Camera	Monochrome Microscopy Camera		#17-812	₹4,01,436 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	LUCID Vision Labs Atlas10 ATX204S-CC, Sony IMX531, 20.4MP, Color Camera	Color Camera		#17-117	₹4,26,393 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	LUCID Vision Labs Atlas10 ATX204S-MC, Sony IMX531, 20.4MP, Monochrome Camera	Monochrome Camera		#17-116	₹4,26,393 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Oryx® ORX-10GS-89S6C-C Color 10GigE	Color Camera		#19-793	₹4,57,722 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Oryx® ORX-10GS-89S6M-C Mono 10GigE	Monochrome Camera		#19-792	₹4,57,722 <a href="#">Request Quote</a>	<a href="#">CONTACT US</a> <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Oryx® ORX-10GS-89S6M-C Mono 10GigE (Recertified 05-P)	Monochrome Camera		#19-792-RCD-05P <b>RECERTIFIED</b>	₹4,77,369 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	BFS-PGE-123S6P-C, Pol. PoE GigE Blackfly® S, Monochrome Camera	Polarized Monochrome Camera		#22-082	₹4,92,768 <a href="#">Request Quote</a>	3 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Oryx® ORX-10GS-123S6C-C Color 10GigE	Color Camera		#19-799	₹4,95,423 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 
<a href="#">MORE+</a> 	Oryx® ORX-10GS-123S6M-C Mono 10GigE	Monochrome Camera		#19-798	₹4,95,423 <a href="#">Request Quote</a>	1 In Stock <input type="text" value="1"/> 