

[See all 11 Products in Family](#)

1.75" Max. Opening, Soft Jaw Pliers



Stock #59-900 **5 In Stock**

1 MRP ₹6,319

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹6,319 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Tip to Tip Distance, Open (mm):
44.45 (1.75")

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Non-Marring Cushioned Tips
- Screw-In Cushioned Tip Design
- Replacement Tips Available

The slip joint design utilized in these pliers is ideal for handling optics, camera-lens assemblies, and other delicate components. Jaw openings range from 1" to 2.75" (dependent on model). Jaws feature screw-in plastic cushions to protect fine knurling and delicate finishes. Tool body is laminated and handles are covered with rolled vinyl to ensure proper grip.

;