

TECHSPEC®

1.7X, 2/3" C-Mount PlatinumTL™ Telecentric Lens



1.7X Magnification, #63-232

Stock **#63-232** 10 TO 12 DAYS

⊖ 1 ⊕

₹136,721.00

ADD TO CART

Qty 1+
₹136,721.00
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
189.50

Horizontal Field of View, 1/2" Sensor:
3.7mm

Horizontal Field of View, 2/3" Sensor:
5.2mm

Filter Thread:
M58 x0.75 (Female)

Maximum Diameter (mm):
60.0

Weight (g): 746
Numerical Aperture NA, Object Side: 0.083
Stock No. of Mounting Clamp: #63-233 Sold Separately
Flange Distance (mm): 17.5
Number of Elements (Groups): 10 (7)
Typical Telecentricity @ 588nm (°): <0.080
Typical Distortion @ 588nm (%): <0.020
Type: Telecentric Lens
Primary Magnification PMAG: 1.7X
Maximum Sensor Format: 2/3"
Working Distance (mm): 123.00
Mount: C-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Depth of Field (mm): ±0.18 at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 5.2 x 3.9
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View