

# 1.8mm Dia, 1550nm DWL, 0.23mm WD, Uncoated, GRIN Lens



Stock #64-532 10 TO 12 DAYS

- 1 +

₹5,003.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| ₹5,003.00                     |
| Qty 11+                       |
| ₹4,437.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Diameter (mm):  
1.80 +0.00/-0.01

Effective Focal Length EFL (mm):  
1.75

Substrate: ☐  
Aluminosilicate Glass Embedded with Silver Ions

f/#:  
0.97

|                                                                     |
|---------------------------------------------------------------------|
| <b>Numerical Aperture NA:</b><br>0.51                               |
| <b>Coating:</b><br>Uncoated                                         |
| <b>Type:</b><br>Gradient Index Lens                                 |
| <b>Wavelength Range (nm):</b><br>1310 - 1550                        |
| <b>Clear Aperture (%):</b><br>90.00                                 |
| <b>Gradient Constant (mm<sup>-1</sup>):</b><br>0.358                |
| <b>Index of Refraction n<sub>d</sub> - Center of Lens:</b><br>1.616 |
| <b>Length (mm):</b><br>4.01                                         |
| <b>Pitch:</b><br>0.23                                               |
| <b>Surface Quality:</b><br>40-20                                    |
| <b>Working Distance (mm):</b><br>0.23                               |
| <b>Working Distance Tolerance (mm):</b><br>±0.01                    |
| <b>Length Tolerance (%):</b><br>±5                                  |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |