

TECHSPEC® 19.1mm Dia., 6.35mm Thick, Fused Silica Uncoated Laser Window Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock **#38-911** 10 TO 12 DAYS

⊖ 1 ⊕ **₹11,528.00**

ADD TO CART

Qty 1-5
₹11,528.00
Qty 6+
₹10,397.00
Volume Pricing
Request Quote

Get Product Downloads



Clear Aperture CA (mm):
17.19

Coating:
Uncoated

Diameter (mm):
19.10 +0.00/-0.10

Substrate: Fused Silica (Coming 7980)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Window Substrate
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): $\lambda/10$
Fused Silica Grade: 7980 0F
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View