

TECHSPEC[®] 19.1mm Dia., 6.35mm Thick, N-BK7 Uncoated Laser Window Substrate



TECHSPEC[®] Uncoated Laser Window Substrates

Stock #38-056 10 TO 12 DAYS

-

1

+

₹10,440.00

ADD TO CART

Qty 1-5
₹10,440.00
Qty 6+
₹9,396.00
Volume Pricing
Request Quote

Get Product Downloads



Clear Aperture CA (mm):
17.19

Coating:
Uncoated

Diameter (mm):
19.10 +0.00/-0.10

Substrate: N-BK7
Index of Refraction n_d: 1.516
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Window Substrate
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 64.17
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): $\lambda/10$
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View