

1.9mm FL, No IR-Cut Filter, f/2, Micro Video Lens



Stock #64-106 10 TO 12 DAYS

- 1 + ₹5,046.00

ADD TO CART

Qty 1-49
₹5,046.00
Qty 50+
₹4,089.00
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
15.20

Filter Thread:
M12 x 0.50

Maximum Diameter (mm):
17.0

Maximum Image Circle (mm):
4.50

Horizontal Field of View @ Max Sensor Format: 118
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 1.90
Maximum Sensor Format: 1/4"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mbunt)
Aperture (f/#): f/2
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

Reach 205: Compliant
Certificate of Conformance: View