

TECHSPEC® 1" Dia, 3" FL Uncoated, Spherical Mirror



Stock **#43-341** 10 TO 12 DAYS

- 1 + **₹8,526.00**

ADD TO CART

Qty 1-9
₹8,526.00
Qty 10+
₹7,265.00
Volume Pricing
Request Quote

Get Product Downloads



Substrate:  **BOROFLOAT®**

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy:

N4
Diameter (inches): 1.0
Diameter (mm): 25.40 +0/-0.3
Diameter Tolerance (inches): +0/-0.01
Effective Focal Length EFL (inches): 3.00
Effective Focal Length EFL (mm): 76.20
Radius of Curvature (mm): 152.40
Aperture (f/#): f/3
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 0.25
Edge Thickness ET (mm): 6.35
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View