

[See all 11 Products in Family](#)

2" Travel, 0.001" Grad., 0.5" Stem Dia. Mic. Drive F-Face



Drive Mechanisms

Stock **#33-737** [CONTACT US](#)

MRP ₹23,306

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹23,306 each
Qty 10-24	₹20,975 each
Need More?	Request Quote

Product Downloads

General

Type:
 English
Manufacturer:
 Mtutoyo

Physical & Mechanical Properties

Travel (inches):
 2

0.001	Graduation (inches):
12	Stem Diameter (mm):
Plain/Flat	Stem/Spindle:
29	Stem Length (mm):
8	Spindle Diameter (mm):
34	Min. Spindle Length (mm):
21	Max. Diameter (mm):
119.5	Overall Length (mm):

Hardware & Interface Connectivity

English Micrometer	Type of Drive:
--------------------	-----------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

