

## 20 lp/mm, 1" x 3", Float Glass, Ronchi Ruling



Stock #38-259 CLEARANCE **6 In Stock**

₹15,930

ADD TO CART

#### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-4    | ₹15,930 each                  |
| Qty 5+     | ₹15,201 each                  |
| Need More? | <a href="#">Request Quote</a> |

#### Product Downloads

#### Physical & Mechanical Properties

|             |                    |
|-------------|--------------------|
| 3.00        | Length (inches):   |
| 12.7 x 25.4 | Pattern Size (mm): |
| 1.10        | Thickness (mm):    |
| 1.00        | Width (inches):    |

#### Optical Properties

---

Vacuum Deposited Chrome **Coating:**

20.00 **Frequency (lp/mm):**

Float Glass **Substrate:**

3.00 **Optical Density OD (Average):**

---

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

---

## Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.

---