

2.0 OD M37 x 0.50, Machine Vision Absorptive ND Filter



Stock #21-567

10 TO 12 DAYS

-

1

+

₹10,353.00

ADD TO CART

Qty 1-9
₹10,353.00
Qty 10+
₹9,866.00
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):

2.0

Clear Aperture CA (mm):

32.50

Filter Thread:

M37 x0.50

Substrate:

ND Filter Glass

Surface Quality: 40-20
Transmission (%): 1.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
