

200 mm Travel, Motorized Linear Stage, Integrated Controller

See More by [Zaber™](#)



#15-288, 200 mm Travel, Motorized Linear Stage, Integrated Controller

Stock **#15-288** 10 TO 12 DAYS

- 1 +

₹237,075.00

ADD TO CART

Qty 1+

₹237,075.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Needle Roller Bearing

Type of Drive:
Precision Lead Screw

Type:
Metric

Stage Size (mm):

45 x 340.4
Travel (mm): 203.2
Accuracy (µm): 60 (Unidirectional)
Backlash (µm): <12
Height (mm): 21
Load Capacity (kg): 10
Manual Control/ LED Indicators: Yes
Manufacturer: Zaber Technologies Inc.
Note: Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232 connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to control simultaneously.
Operating Temperature (°C): 0 - 50
Parallelism (µm): <25
Power Supply: Power Supply Required and Sold Separately. USA: #15-294 Europe: #15-294 Japan: #23-662 Korea: #33-773 China: #15-294
Repeatability (µm): <3
Resolution (µm): 0.05
Speed (mm/s): 0.00003 to 26
Type of Motor: 2-Phase Stepper
Weight (kg): 0.44
Computer Interface: USB with #15-295 RS-232 with #15-297
Maximum Operating Current (mA): 350

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant