


[See all 14 Products in Family](#)

2000µm with 1 Fiber, Optical Grade Plastic Light Guide



Stock #02-551 [CONTACT US](#)

⊖ 1 ⊕ ₹428

[ADD TO CART](#)

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | ₹428 each |
| Need More? | Request Quote |

Product Downloads

Physical & Mechanical Properties

75.00 **Minimum Bend Radius (mm):**

1.00 **Number of Fibers:**

3.0 **Outer Diameter (mm):**

1960.00 **Core Diameter (µm):**

Cut to Order, Minimum 10 **Length (ft):**

Black Polyethylene Jacket **Construction:**

Diameter Tolerance (%):
±6

Optical Properties

Acceptance Angle (°):
60.00

Substrate:
Acrylic

Attenuation (dB/m):
0.22

Numerical Aperture NA:
0.50

Fiber Diameter (µm):
2000.00

Index of Refraction (n₁) - Core:
1.49

Index of Refraction (n₂) - Cladding:
1.402

Attenuation (dB/km):
150 - 300 (@650nm)

Numerical Aperture (NA) Tolerance:
±0.03

Environmental & Durability Factors

Operating Temperature (°C):
-55 to +70

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)

Country of Origin:
Japan

Imported By:
Edmund Optics India Private Limited

Product Details

Price listed is per foot - minimum order is 10 feet per stock number. 3mm Fiber is lower grade ESKA® fiber for commercial applications only.

- Superior Light Transmission
- ESKA® Fiber Strands
- Step Index

Optical Grade Fiber Optics, developed and manufactured by Mitsubishi, are offered in two grades, both with superior optical properties for improved transmission. The core of both is made of acrylic polymer PMMA (polymethyl-methacrylate) and is sheathed with a particular thin layer of fluorine polymer which has a lower refractive index than the fiber core. Optical Grade Fiber Optics are designed to provide higher transmission in the visible region of the spectrum. They can be used for a wide range of applications, from general industrial light guides to short-distance data transmission. The fiber is tough and flexible but is not designed to bear loads.

Note: Price listed is per foot - minimum order is 10 feet per stock number. 3mm Fiber is lower grade ESKA® fiber for commercial applications only.

Technical Information

