

TECHSPEC[®] 20mm 1064nm, Laser Line λ /20 High Tolerance Right Angle Mirror



Stock #37-664 10 TO 12 DAYS

-

1

+

₹22,881.00

ADD TO CART

Qty 1-5
₹22,881.00
Qty 6+
₹18,314.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
 λ /20

Substrate:
[Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Length of Legs (mm):

20.00
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R _{abs} >99.8% @ 1064nm @45° AOI R _{avg} >99.5% @ 1046 - 1074nm @ 45° AOI
Coating: Laser Mirror (1064nm)
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Design Wavelength DWL (nm): 1064
Length of Hypotenuse (mm): 28.30
Type: Right Angle Mirror
Pyramid Tolerance (arcmin): ±1
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference:  1MW/cm² @ 1064nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View