

TECHSPEC® 20mm - 30mm Length, C-Mount Fine Focus Tube



Stock #58-756 **16 In Stock**

⊖ 1 ⊕ ₹7,848

ADD TO CART

Volume Pricing

Qty 1-4	₹7,848 each
Qty 5-9	₹6,939 each
Qty 10-25	₹6,403 each
Need More?	Request Quote

Product Downloads

General

Fine Focus Tube **Type:**

Extension Tube (Adjustable) **Function:**

Physical & Mechanical Properties

20.0 - 30.0 **Extension Length (mm):**

30.0 **Outer Diameter (mm):**

18.0 **Clear Aperture CA (mm):**

18.0 **Inner Diameter (mm):**

Threading & Mounting

M18 x 0.5 **Barrel Thread:**

C-Mount **Thread Type:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 235:**

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

Note: Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

Technical Information

