

TECHSPEC[®] 20mm, 632.8nm, Lateral Displacement Polarizing Beamsplitter



Lateral Displacement Beamsplitters

Stock #47-191 10 TO 12 DAYS

-

1

+

₹61,335.00

ADD TO CART

Qty 1-5
₹61,335.00
Qty 6+
₹49,068.00
Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (arcsec):
±5

Beam Separation (mm):
20.00

Clear Aperture (%):
80.00

Coating Specification:

R _{abs} <0.3% @ 632.8nm
Construction: Prism
Design Wavelength DWL (nm): 632.8
Dimensional Tolerance (mm): ±0.1
Extinction Ratio: >1000:1
P-Polarization Transmission (%) : >95
Parallelism (arcmin): <2
S-Polarization Reflection (%) : >99
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Linear Polarizer
Type of Optics: Polarizing

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View