

TECHSPEC[®] 20mm 980nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-883** CLEARANCE 10 TO 12 DAYS

-

1

+

₹8,696.00

ADD TO CART

Qty 1+

₹8,696.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification:
R_{abs} <0.25% @ 980nm

Construction:
Cube

Design Wavelength DWL (nm): 980
Dimensions (mm): 20.0 x 20.0 x 20.0 ±0.1
Extinction Ratio: 1000:1
P-Polarization Transmission (%): >90
S-Polarization Reflection (%): >99.5
Substrate: ☐ N-BK7
Surface Flatness (P-V): $\lambda/4$
Surface Quality: 40-20
Type: Linear Polarizer

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View