

TECHSPEC[®] 20mm Dia. x 20mm FL, YAG-BBAR Coated, Inked, Double-Convex Lens



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock **#89-257-INK** 17 TO 22 D=DAYS

- 1 +

₹5,003.00

ADD TO CART

Qty 1-9

₹5,003.00

Qty 10+

₹4,502.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
20.00 ±0.025

Back Focal Length BFL (mm):
18.55

Effective Focal Length EFL (mm): 20.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R_{abs} <0.25% @ 532nm R_{abs} <0.25% @ 1064nm R_{avg} <1.0% @ 500 - 1100nm
Substrate:  N-SF11
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.6
Radius R₁=R₂ (mm): 30.25
Clear Aperture CA (mm): 19.00
f/#: 1.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.50
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 2500

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View