

20mm Diameter, 0° AOI, Hot Mirror



Hot Mirrors

Stock #62-625 10 TO 12 DAYS



1



₹3,654.00

ADD TO CART

Qty 1-9

₹3,654.00

Qty 10+

₹3,202.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):
0.00

Coating:
Hot Mirror, 0°

Diameter (mm):
20.00 ±0.25

Substrate:

[BOROFLOAT®](#)

Reflection (%):
>95, 750 - 1150nm

Surface Quality:
80-50

Thickness (mm):
1.10

Transmission (%):
>90, 425 - 675nm

Type:
Shortpass Filter

Coating Specification:
Surface 1: 0° Hot Mirror
Surface 2: None

Wavelength Range (nm):
425 - 1150

Surface Flatness (P-V):
4 - 6λ

Coating Type:
Dielectric

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
