

TECHSPEC® 20mm Enhanced Aluminum Coated, UV Fused Silica Right Angle Mirror



Stock #22-549 10 TO 12 DAYS

- 1 + **₹19,575.00**

ADD TO CART

Qty 1-5
₹19,575.00
Qty 6+
₹15,660.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):

λ/20

Substrate:

[Fused Silica](#) (Corning 7980)

Surface Quality:

20-10

Length of Legs (mm):

20.00
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 25.45 x 18.00
Length of Hypotenuse (mm): 28.30
Type: Right Angle Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant