

TECHSPEC® 20mm NIR, 70R/30T, Non-Polarizing Cube Beamsplitter



Stock #13-439 10 TO 12 DAYS

- 1 + **₹20,793.00**

ADD TO CART

Qty 1-5
₹20,793.00
Qty 6+
₹16,443.00
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:

NIR
Coating Specification: R _{avg} <0.5% @ 720 - 1080nm
Construction: Cube
Dimensions (mm): 20.0 x 20.0 x 20.0 ±0.1
Reflection/Transmission Ratio (R/T): 70/30
Substrate:  N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 720 - 1080
[Ts-Tp]: <6%
Absolute Transmission (%): 27 ±10
Average Transmission (%): 27 ±5
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View