


TECHSPEC®

20mm UV Enhanced Aluminum Coated, N-BK7 Right Angle Prism



Stock #24-181 [CONTACT US](#)

-

1

+

₹9,135.00

ADD TO CART

Qty 1-5
₹9,135.00
Qty 6+
₹7,308.00
Volume Pricing
Request Quote

Get Product Downloads



Substrate: ☐ N-BK7

Surface Quality: 60-40

Length of Legs (mm): 20.00

Dimensional Tolerance (mm):

±0.1
Coating Specification: R _{avg} >85% @ 250 - 700nm R _{avg} >89% @ 250 - 450nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 25.45 x 18.00
Length of Hypotenuse (mm): 28.30
Type: Right Angle Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference:  0.5 J/cm² @ 355nm, 10ns
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant