

20X Focusing Lens



20X Focusing Lens



Stock **#28-780** **5 In Stock**

⊖ 1 ⊕ ₹35,550

ADD TO CART

Volume Pricing	
Qty 1+	₹35,550 each
Need More?	Request Quote

Product Downloads

General

Note:
Use with #15-944 instead of #18-509 for uniform in-line illumination.

Physical & Mechanical Properties

Length (mm):

95.55

Maximum Diameter (mm):

35.00

Threading & Mounting

Mounting Threads:
M29 x 0.75

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited

Product Details


- Up to 43% Smaller than Industry Standard Systems
- Optimized Performance up to 1.1" Sensor
- Ideal for Life Science and Industrial Applications
- Winner of the [2023 Bronze VSD Innovators Award](#)

Edmund Optics® 120i Plan APO Infinity Corrected Objectives are infinite conjugate microscope objectives that offer exceptional image flatness and chromatic correction over 400-700nm. These objectives were designed for a 1.1" sensor to offer a large field of view and reliable image quality for high-throughput imaging applications. Ideal for life science and machine vision applications such as microscopy, flow cytometry, pharmaceutical inspection, and assembly line or fault inspection.

These objectives won the [2023 Bronze VSD Innovators Award](#).

Technical Information

Compact Tube Lens System



Standard Tube Lens System

