

TECHSPEC[®] 21 x 30mm UV Enhanced Aluminum, λ/4 Mirror



Stock #46-717 10 TO 12 DAYS

-

1

+

₹4,785.00

ADD TO CART

Qty 1-5
₹4,785.00
Qty 6+
₹3,828.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate:
[BOROFLOAT[®]](#)

Back Surface:
Fine Grind

Surface Quality:

60-40
Dimensions (mm): 21.0 x 30.0
Dimensional Tolerance (mm): +0.0/-0.5
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0.0
Type: Flat Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Length (mm): 30.00
Width (mm): 21.00
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant