

## 2.15" White, LED Darkfield Illuminator

See More by [Advanced Illumination](#)



Stock #66-790 10 TO 12 DAYS

- 1 + **₹34,713.00**

ADD TO CART

Qty 1+

₹34,713.00

Volume Pricing

[Request Quote](#)

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:

White

Height (mm):

19.0

Inner Diameter (mm):

19.0

Model Number:

RL2115-VHI-24

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Mount:</b><br>Standard                                                                                                                                                                                                                   |
| <b>Operating Temperature (°C):</b><br>0 to +65                                                                                                                                                                                              |
| <b>Outer Diameter (mm):</b><br>55.0                                                                                                                                                                                                         |
| <b>Mounting Threads:</b><br>M3 x2                                                                                                                                                                                                           |
| <b>Working Distance (mm):</b><br>19 - 25.4                                                                                                                                                                                                  |
| <b>LED Lifetime (hours):</b><br>50,000                                                                                                                                                                                                      |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#66-855</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> |
| <b>Number of LEDs:</b><br>15.00                                                                                                                                                                                                             |
| <b>Number of Channels:</b><br>1.00                                                                                                                                                                                                          |
| <b>Field Coverage (mm):</b><br>6.4 - 12.7                                                                                                                                                                                                   |
| <b>Maximum Trigger Frequency (Hz):</b><br>30.00                                                                                                                                                                                             |
| <b>Type of Illumination:</b><br>LED Illuminator                                                                                                                                                                                             |
| <b>Note:</b><br>Requires a 24V power supply <a href="#">#66-855</a> . European power supply <a href="#">#35-200</a> also available.                                                                                                         |
| <b>Manufacturer:</b><br>Advanced Illumination                                                                                                                                                                                               |
| <b>Geometry:</b><br>Ring Light                                                                                                                                                                                                              |
| <b>Illumination Mode:</b><br>Constant                                                                                                                                                                                                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |