

TECHSPEC® 22 x 22mm Protected Silver, λ/4 Mirror



Stock **#46-723** 10 TO 12 DAYS

- 1 + **₹5,873.00**

ADD TO CART

Qty 1-5
₹5,873.00
Qty 6+
₹4,698.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: 
BOROFLOAT®

Back Surface:
Commercial Polish

Surface Quality:

60-40
Dimensions (mm): 22.0 x 22.0
Dimensional Tolerance (mm): +0.0/-0.5
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 5.00 +0.5/-0.0
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Length (mm): 22.00
Width (mm): 22.00
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant