

2.25" x 12.0", 2.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock #46-616 **20+ In Stock**

⊖ 1 ⊕ ₹6,968

ADD TO CART

Volume Pricing

Qty 1-10	₹6,968 each
Qty 11-49	₹6,267 each
Need More?	Request Quote

Product Downloads

General

Fresnel Lens **Type:**

Physical & Mechanical Properties

0.06 **Center Thickness CT (inches):**

±0.05 **Dimensional Tolerance (inches):**

Dimensions (inches):

2.25 x 12.00

Dimensions (mm):

57.15 x 304.8

Effective Size (inches):

2.0 x 12.0

Thickness Tolerance (inches):

±0.020

Optical Properties

Effective Focal Length EFL (mm):

50.80

Substrate:

Acrylic

Coating:

Uncoated

Wavelength Range (nm):

400 - 1100

Effective Focal Length EFL (inches):

2.00

Groove Density (grooves/inch):

200.00

Index of Refraction (n_d):

1.49

Transmission (%):

85 (Typical)

Environmental & Durability Factors

Operating Temperature (°C):

80 (Maximum)

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 242:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited

Product Details

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

Technical Information

